






This software is designed for measuring void percentage of semiconductor I.C, wire pitch, wire sweep and BGA solder ball area. Measuring result are converted automatically into actual dimensions an any ranges of magnification, and displayed on the monitor with statistics all of which can be filled.



CUSTOMER SUPPORT

You can consult anything with SOFTEX staff who specialized in the apparatus. We have also "System laboratory service", where we provide you trial and training.

※Published specifications and product appearance are subject to change without notice.

We are flexible to make special designed machine. FOR EXSAMPLE...

- Computerized X-ray control
- Computerized table control
- Fully automatic inline system
- Table tilting mechanism



SOFTEX CO., LTD.

5-19-18 HIGASHI KASHIWAGAYA, EBINA-CITY,
KANAGAWA PREF, 243-0401, JAPAN
TEL : 81-46-232-2571
FAX : 81-46-232-1179
E-mail : overseas@softex-kk.co.jp
URL : http://www.softex-kk.net/



Has an ability to provide sharp and clear images of minute defects in the BGA, CSP, and Electric devices, voids and cracks in plastic packages.

**SOFTEX original micro focus X-ray Generator is equipped!
Realizes sharp and clear images!**

FEATURES

- Equips high resolution X-ray I.I. camera.
- Realizes high resolution.
- High-performance zoom system.
- Installs SOFTEX imaging and measurement software, ZET-1.
- High-performance table system to get sharp images.
- Perfect X-ray proof cabinet, leakage is less than 1 μ Sv/h.

Function of ZET-1	Measurement	Image processing	Image saving	Table inching	Table teaching	Index function
-------------------	-------------	------------------	--------------	---------------	----------------	----------------



Standard type


- SOFTEX original micro focus X-ray generator is equipped.
- Easy to control the table with joystick.
- Possible to enlarge the table size as a option.

F type

- A high-performance micro focus X-ray generator is equipped.
- A compact body.
- Possible to control with standing position.

OPTIONS

- Possible to observe samples from multi-angle with the table inclining system.
- Equips the camera driving system (up / down) to get wide field of view.
- Easy to get multi-angle images to use the sample manipulator or sample rolling system.



SPECIFICATION

MODEL	WORK-LEADER 901	WORK-LEADER 905
Input	AC100-240V 50/60Hz ※note.1	
Max tube voltage	90kV	
Max tube current	100 μ A	
Power consumption	approx. 1kVA	
Total resolution	More than 33.3 L p/mm	
Focus size	10 μ m	5 μ m
Table size	X250×Y330mm ※note.2	
Drive confine (X-Y table)	X250×Y330×Z300mm ※note.2	
Drive confine (Camera up & down)	Option : 400mm ※note.3	
X-ray leakage	Less than 1 μ Sv/h	
Size	Standard type	Main unit : W 750×D1,100×H1,950mm Control cabinet : W700×D1,000×H1,400mm
	F type	Main unit : W1,130×D1,100×H1,950mm
Weight	Standard type : Approx. 950kg	F type : Approx. 850kg

note.1 : It could be three phase /200V by the specification.

note.2 : 400×400mm, 600×600mm can be available.

note.3 : Camera Up & Down 600mm is available, in such case Z table drive is 200mm.

※ Standard type and F type of 901・905.